



YGHP34C2 Figure 6 Compression Grounding Connector

By Burndy
Catalog # YGHP34C2



Cu Compression Ground Rod Connector, #4 Sol - #2 Str, 5/8" - 3/4" Rod Dia.

Application

For Direct Burial In Earth And Concrete

General

Connector Type	Tap
Die Index	998
EU RoHS Indicator	Yes
Material	Copper
Oxide Inhibitor Type	Penetrox E
Physical Attribute - Number of Crimps Required	1
Plated	N
Plating Type	Unplated
Prefilled Oxide Inhibitor	Y
Sub Brand	HYTAP
Trade Name	HYTAP™
Type	Taps
UPC	781810220955
UPC 12 Digit	7818102209555

Dimensions

Dimension - B Length fraction	3/4 in
Dimension - B Length inch	0.75 in

Conductor Related

Conductor - Copper Solid Tap	4 AWG;3 AWG;2 AWG
Conductor - Copper Solid Tap Range	4 AWG-2 AWG
Conductor - Copper Str Run	250 kcmil;300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil
Conductor - Copper Str Run Range	250 kcmil-500 kcmil
Conductor - Copper Str Tap	4 AWG;3 AWG;2 AWG
Conductor - Copper Str Tap Range	4 AWG-2 AWG
Conductor - Rebar Run	5 ;6
Conductor - Rebar Run Range	5 -6
Conductor - Rod Run	5/8 in;3/4 in
Conductor - Rod Run Range	5/8 in-3/4 in

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	<ul style="list-style-type: none"> • UL467 • IEEE 837 • IEEE 837 2014 Qualified
Standards - Industry Standards Met	UL467;IEEE 837;IEEE 837 2014 Qualified
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	25
Minimum Pack Quantity	1
Pallet Quantity	4625

Product Assets

- [3D Models - YGHP34C2_MODEL-IGES](#)
- [3D Models - YGHP34C2_MODEL-STEP](#)
- [3D Models - YGHP34C2_MODEL-PDF](#)
- [Catalogs - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Sales Drawings - sd082473-01](#)



A proud member of the Hubbell Family.

