
# UL LISTED POWER DISTRIBUTION BLOCKS

## VERSIPOLE™

These Power Distribution Blocks are Listed to the Power Distribution Block Standard UL 1953. They contain the same features and characteristics as the non-Listed blocks however, these have spacings that are suitable for installations in most industrial control panel feeder and branch circuits, HVAC systems, and Wireways (with optional cover; sold separately). They are available in one, two, or three pole configurations. An "Adder" is also available with optional End Barrier (sold separately), to allow user customized configurations.






## Features & Benefits

- Single or dual run connections allow the user to minimize the number of connections required
- Suitable for use with aluminum or copper conductors providing maximum versatility
- Available in 3 sizes for optimization of space
- 600V, ALCU Rated; meets or exceeds industry standard requirements
- Range taking designs to accommodate wire sizes up to 600 kcmil
- High Short-Circuit Rating up to 100kA with proper fusing
- Meets spacing requirements of Industrial Control Panel Standard UL 508A (spacing of 1" through air and 2" over surface)
- Adders and End Barriers available separately for all 3 sizes providing capability to create as many poles as required
- Hinged Covers available separately to cover 3 sizes providing user protection and easy access to connector terminal block

[1] Short-Circuit Current Rating with proper fusing

## Small Series:

| Catalog Number | Connector | | Run | Tap | Width | Height | Depth | Ampere Rating per Pole | Number of Poles | SCCR[1] |
|---|---|---|---|---|---|---|---|---|---|---|
| | Number of Run(s) | Number of Tap(s) | Wire Range AL9CU | Wire Range AL9CU | | | | | | |
| **BDCSHC142/01** | 1 | 4 | 14-2/0 | 14-4 | 1.05 | 2.81 | 3.08 | 175 | 1 | 100kA |
| **BDASHC142/01** | 1 | 4 | 14-2/0 | 14-4 | 0.93 | 2.81 | 3.08 | 175 | Adder | 100kA |
| **BDCSHC112/01** | 1 | 1 | 14-2/0 | 14-2/0 | 1.05 | 2.81 | 3.08 | 175 | 1 | 100kA |
| **BDASHC112/01** | 1 | 1 | 14-2/0 | 14-2/0 | 0.93 | 2.81 | 3.08 | 175 | Adder | 100kA |


## Small Series Hinged Cover and End Barrier:

| Catalog Number | Description |
|---|---|
| **BDASHCEB** | End Barrier for Small Series Adder Distribution Blocks |
| **BDBSHCCOVER** | Hinged Cover for use with Small Series Distribution Blocks and Adders (use of End Barrier necessary with Adders to attach cover). Order 1 cover per pole |

**Blue highlighted items are industry standard and most frequently ordered.**

# UL LISTED POWER DISTRIBUTION BLOCKS

## VERSIPOLE™



## Medium Series:

| Catalog Number | Connector | | Run | Tap | Width | Height | Depth | Ampere Rating per Pole | Number of Poles | SCCR[1] |
|---|---|---|---|---|---|---|---|---|---|---|
| | Number of Run(s) | Number of Tap(s) | Wire Range AL9CU | Wire Range AL9CU | | | | | | |
| BDBMHC162/01 | 1 | 6 | 14-2/0 | 14-2 | 1.85 | 3.25 | 5 | 175 | 1 | 100kA |
| BDBMHC162/02 | 1 | 6 | 14-2/0 | 14-2 | 3.57 | 3.25 | 5 | 175 | 2 | 100kA |
| BDBMHC162/03 | 1 | 6 | 14-2/0 | 14-2 | 5.28 | 3.25 | 5 | 175 | 3 | 100kA |
| BDAMHC162/0 | 1 | 6 | 14-2/0 | 14-2 | 1.72 | 3.25 | 5 | 175 | Adder | 100kA |
| BDBMHC112/01 | 1 | 1 | 14-2/0 | 14-2/0 | 1.85 | 3.25 | 5 | 175 | 1 | 100kA |
| BDBMHC112/02 | 1 | 1 | 14-2/0 | 14-2/0 | 3.57 | 3.25 | 5 | 175 | 2 | 100kA |
| BDBMHC112/03 | 1 | 1 | 14-2/0 | 14-2/0 | 5.28 | 3.25 | 5 | 175 | 3 | 100kA |
| BDAMHC112/0 | 1 | 1 | 14-2/0 | 14-2/0 | 1.72 | 3.25 | 5 | 175 | Adder | 100kA |
| BDBMHC113501 | 1 | 1 | 6-350 | 6-350 | 1.85 | 3.25 | 5 | 310 | 1 | 100kA |
| BDBMHC113502 | 1 | 1 | 6-350 | 6-350 | 3.57 | 3.25 | 5 | 310 | 2 | 100kA |
| BDBMHC113503 | 1 | 1 | 6-350 | 6-350 | 5.28 | 3.25 | 5 | 310 | 3 | 100kA |
| BDAMHC11350 | 1 | 1 | 6-350 | 6-350 | 1.72 | 3.25 | 5 | 310 | Adder | 100kA |
| BDBMHC262/01 | 2 | 6 | 14-2/0 | 14-2 | 1.85 | 3.25 | 5 | 350 | 1 | 100kA |
| BDBMHC262/02 | 2 | 6 | 14-2/0 | 14-2 | 3.57 | 3.25 | 5 | 350 | 2 | 100kA |
| BDBMHC262/03 | 2 | 6 | 14-2/0 | 14-2 | 5.28 | 3.25 | 5 | 350 | 3 | 100kA |
| BDAMHC262/0 | 2 | 6 | 14-2/0 | 14-2 | 1.72 | 3.25 | 5 | 350 | Adder | 100kA |
| BDBMHC222/01 | 2 | 2 | 14-2/0 | 14-2/0 | 1.85 | 3.25 | 5 | 350 | 1 | 100kA |
| BDBMHC222/02 | 2 | 2 | 14-2/0 | 14-2/0 | 3.57 | 3.25 | 5 | 350 | 2 | 100kA |
| BDBMHC222/03 | 2 | 2 | 14-2/0 | 14-2/0 | 5.28 | 3.25 | 5 | 350 | 3 | 100kA |
| BDAMHC222/0 | 2 | 2 | 14-2/0 | 14-2/0 | 1.72 | 3.25 | 5 | 350 | Adder | 100kA |
| BDBMHC145001 | 1 | 4 | 4-500 | 14-2/0 | 1.85 | 3.25 | 5 | 380 | 1 | 100kA |
| BDBMHC145002 | 1 | 4 | 4-500 | 14-2/0 | 3.57 | 3.25 | 5 | 380 | 2 | 100kA |
| BDBMHC145003 | 1 | 4 | 4-500 | 14-2/0 | 5.28 | 3.25 | 5 | 380 | 3 | 100kA |
| BDAMHC14500 | 1 | 4 | 4-500 | 14-2/0 | 1.72 | 3.25 | 5 | 380 | Adder | 100kA |
| BDBMHC1625001 | 1 | 6 | 4-500 | 14-2 | 1.85 | 3.25 | 5 | 380 | 1 | 100kA |
| BDBMHC1625002 | 1 | 6 | 4-500 | 14-2 | 3.57 | 3.25 | 5 | 380 | 2 | 100kA |
| BDBMHC1625003 | 1 | 6 | 4-500 | 14-2 | 5.28 | 3.25 | 5 | 380 | 3 | 100kA |
| BDAMHC162500 | 1 | 6 | 4-500 | 14-2 | 1.72 | 3.25 | 5 | 380 | Adder | 100kA |

## Medium Series Hinged Cover and End Barrier:

| Catalog Number | Description |
|---|---|
| BDAMHCEB | End Barrier for Medium Series Adder Distribution Blocks |
| BDBMHCCOVER | Hinged Cover for use with Medium Series Distribution Blocks and Adders (use of End Barrier necessary with Adders to attach cover). Order 1 cover per pole |

**Blue highlighted items are industry standard and most frequently ordered.**