2.94 in (75 mm)



Shown actual size: Skylark dimmer and 1-gang Claro wallplate in White (WH).

Product family features

- Rocker switch returns light to your favorite light level
- Slide up to brighten, down to dim (adjust light to suit any activity)
- · eco-dim_® model available
- 1000W preset dimmers have voltage compensation which maintains stable light levels, despite line voltage variations
- · 100% factory tested
- Coordinating Claro® and Stainless Steel wallplates only available separately
- Custom engraving available for wallplates, see pg. 155

Control types

Single-pole (one location)

a-way or 4-way (two or more locations)

Direct load type compatibility

- ▼ Magnetic low-voltage lighting
- ☐ Electronic low-voltage lighting
- LED lighting
- Dimmable compact fluorescent
- Ceiling fans
- ★ Ceiling fan/lights

Load type requiring load interface

Neon/cold cathode lighting

Lighting load interfaces may be applicable for some additional load type, voltage and capacity combinations.

For additional information, see pg. 174.

Available finishes

Use **BOLD** color code in model number (Example: S-600P-**GR**) Gloss finishes*



^{*}Coordinating wallplates only available separately. For wallplate information, see pg. 160.

Stainless Steel wallplate includes black plastic trim/adapter, visible from side. Match with separate Black (BL) controls.

Dimmers

Slide-to-off dimmers



 Slide up to on/brighten; down to dim/off

Dimmers with on/off switch and locator light



- · Rocker switch turns on/off
- Slide up to brighten; down to dim
- · Includes amber locator light

Dimmers with on/off switch



- · Rocker switch turns on/off
- Slide up to brighten; down to dim
- eco-dim_® model guarantees at least 15% energy savings compared to a standard switch

Skylark_® dimmers and fan controls

Fan and fan/light controls

Slide-to-off fan controls



- Slide up to on/increase speed; down to decrease/off
- 3-quiet fan speeds for increased comfort
- For use with only one ceiling paddle fan
- Quiet 3-speed designed to prevent motor hum
- Fully variable model also available

Dual devices

Dual slide-to-off dimmers (two loads)



Dimmers (left/right)

 Slide up to on/brighten; down to dim/off

Slide-to-off fan controls with on/off light switch



Fan control (top)

- Slide up to on/increase fan speed; down to decrease fan speed/off
- 3-quiet fan speeds for increased comfort
- For use with only one ceiling paddle fan
- Quiet 3-speed designed to prevent motor hum

Switch (bottom)

· Rocker switch turns light on/off

Dual slide-to-off fan control and dimmer



Fan control (left)


- Slide up to on/increase speed; down to decrease/off
- 3-quiet fan speeds for increased comfort
- Quiet 3-speed designed to prevent motor hum
- Fully variable available for use with multiple paddle or exhaust fans

Dimmer (right)

 Slide up to on/brighten; down to dim/off


Connections overview

Load connections*



Control types (for 2 or more locations)

Dim from one location, switch from the others



For more information on ballasts, visit **www.lutron.com/ballasts**. For more information on LED drivers, visit **www.lutron.com/LED**.

*For illustration purposes only. Consult model number pages for specific voltage and capacity information.

Dimmer model numbers

Dimmers with on/off switch

Single-pole	S-600P- <u>CC</u> ³
120V 600W	
Single-pole	S-10P- <u>CC</u> 3
120V 1000W	
3-way	S-603P- <u>CC</u> ³
120V 600W	
3-way	S-103P- <u>CC</u> 3
120V 1000W	

eco-dime dimmer with on/off switch

3-way/single-pole	S-603PG- EE 2
120V 600W	

eco-dim model guarantees at least 15% energy savings compared to a standard switch.

Dimmers with on/off switch and locator light

Single-pole	S-600PNL- <u>CC</u> 3
120V 600W	
Single-pole	S-10PNL- <u>CC</u> 3
120V 1000W	
3-way	S-603PNL- <u>CC</u> 3
120V 600W	
3-way	S-103PNL- <u>CC</u> 3
120V 1000W	

Slide-to-off dimmers

Single-pole	S-600- CC 3
120V 600W	
Single-pole	S-1000- <u>CC</u> ³
120V 1000W	

For dual slide-to-off dimmers (two loads), see page 111.

▼ Magnetic low-voltage dimmers

Dimmers with on/off switch

Single-pole	SLV-600P- CC 3
120V 600VA (450W)	
3-way	SLV-603P- CC 3
120V 600VA (450W)	

The stated VA (Volt-Ampere) rating includes the magnetic transformer heat losses and the lamp load. The stated W (Watt) rating is the maximum lamp wattage based on assumed 20% transformer loss.

□ Electronic low-voltage dimmers*

Dimmers with on/off switch

Single-pole	SELV-300P- <u>CC</u> 3
120V 300W	
3-way	SELV-303P- CC ³
120V 300W	
•	

Certain LED drivers are dimmable using an ELV dimmer, for more information, visit www.lutron.com/LED.

CC³: Gloss color codes, see pg. 105

EE²: Available in White (WH), Ivory (IV), Almond (AL) and Light Almond (LA) (Wallplates not included, order separately, see pg. 160)

All models must be derated if ganged unless otherwise noted, see pg. 170.

Dimmer model numbers

Z 3-wire fluorescent dimmers*

Dimmers with on/off switch

Single-pole	SF-10P- <u>CC</u> ³
120V 8A	
Single-pole	SF-12P-277- CC 3
277V 6A	
3-way	SF-103P- <u>CC</u> ³
120V 8A	
3-way	SF-12P-277-3- <u>CC</u> 3
277V 6A	

For use with Hi-lume®, Hi-lume® Compact SE, Hi-lume® 3D, Eco-10®, EcoSystem® ballasts.

No derating required if ganged.

Adjustable low-end trim.

Dimmers with on/off switch

Single-pole	SF-10P- CC ³
120V 8A	
Single-pole	SF-12P-277- <u>CC</u> 3
277V 6A	
3-way	SF-103P- <u>CC</u> ³
120V 8A	
3-way	SF-12P-277-3- <u>CC</u> 3
277V 6A	

For use with Hi-lume LED driver only.

For more information on Hi-lume LED drivers, visit **www.lutron.com/HilumeLED**.

No derating required if ganged.

Adjustable low-end trim.

☐ Tu-Wire® fluorescent dimmers

Dimmers with on/off switch

3-way/single-pole	SFTU-5A3P- <u>CC</u> 3
120V 5A	
Also compatible with Advance Mark X	

ballasts, for further information, visit

www.lutron.com/advance.

For information on use with Universal and OSRAM ballasts, contact Technical Support at 1.800.523.9466.

CC³: Gloss color codes, see pg. 105 (Wallplates not included, order separately, see pg. 160)

For more information on ballasts, visit www.lutron.com/ballasts.

All models must be derated if ganged unless otherwise noted, see pg. 170.

Fan control model numbers

★ Fan controls

Slide-to-off fan controls—quiet 3-speed

Single-pole SFSQ-F-CC3 120V 1.5A Single-pole SFSQ-F-HO-CC³

120V 2.0A

For use with only one ceiling paddle fan.

SFSQ-F-HO- for use with Hunter Original Series.

Slide-to-off fan control—fully variable

SFS-5E-CC3 Single-pole 120V 5A

For use with multiple ceiling paddle fans or exhaust fans.

Fan/light controls

Fan control—quiet 3-speed and dimmer

Single-pole fan control S2-LFSQ-CC³ 120V 1.5A (left)

120V single-pole dimmer 300W (right)

For use with only one ceiling paddle fan.

Fan control—fully variable and dimmer

Single-pole fan control S2-LF-**CC**3 120V 2.5A (left)

120V single-pole dimmer 300W (right)

For use with multiple ceiling paddle fans.

Fan control/light switch

Fan control—quiet 3-speed and switch

SFSQ-LF-CC³ Single-pole fan control 120V 1.5A (top) 120V single-pole switch 360W (bottom) (incandescent/halogen loads only)

CC³: Gloss color codes, see pg. 105 (Wallplates not included, order separately, see pg. 160)

All models must be derated if ganged unless otherwise noted, see pg. 170.

Dual device model numbers

√ Incandescent/halogen and Incandescent/halogen dimmers

Dual slide-to-off dimmers (two loads)

Single-pole S2-L-**CC**³
120V 300W light (left)
incandescent/halogen
120V 300W light (right)
incandescent/halogen

Replacement knob model numbers

Knobs

Single-pole	SK- <u>EE</u> ²
Standard knob	
Split knobs	contact customer service

CC³: Gloss color codes, see pg. 105 (Wallplates not included, order separately, see pg. 160)


EE²: Available in White (WH), Ivory (IV), Almond (AL) and Light Almond (LA)

All models must be derated if ganged unless otherwise noted, see pg. 170.

Accessories

Wallplates


4.75 in (121 mm)



Shown actual size: 2-gang Claro® wallplate in White (WH). For more information about Designer wallplates, see pg. 160.

Coordinated electrical devices








For more information about coordinated Designer electrical devices, see pg. 163.

6-port frame

Wallplates and accessories | Designer | Claro / Satin Colors



Product family features

- Can be used in conjunction with the following dimmer(s) and switch(es):
 Maestro®, Maestro IR®, Maestro Wireless®,
 Pico™ wireless control, Spacer System®,
 Diva®, Lyneo® Lx, Skylark®, Skylark Contour™
- All Lutron® wallplates are screwless, seamless and have no visible hardware; the front plate securely snaps into the alignment adapter plate
- Full line of wiring devices in designer style opening
- Blank inserts available for Gloss colors (DV-BI-) and Satin colors (SC-BI-)
- Customize your designer wallplate with engraving, contact customer service to get started at 1.888.LUTRON1

Ganging and derating

- · Designer wallplates use standard ganging
- Requires fins to be removed from dimmers for proper spacing ("Fins Broken" ganging), see pg. 170
- May require derating (i.e., reduction of dimmer capacity due to fin removal), see Derating Tables, pg. 172

Available finishes

Use ${f BOLD}$ color code in model number (Example: SC-1- ${f PL}$)

Gloss finishes



Satin finishes



^{*}Stainless Steel finish wallplates include black plastic trim/adapter, visible from side. Match with separate Black (BL) or Midnight (MN) controls and accessories.

Wallplates for Maestro®, Maestro IR®, Maestro Wireless®, Pico™ wireless control, Spacer System®, Diva®, Lyneo® Lx, Skylark® and Skylark Contour™




1-gang*

CW-1-<u>**CC**</u>² SC-1-<u>**CC**⁴</u>

W: 2.94 in (75 mm); H: 4.69 in (119 mm)


D: .30 in (7.6 mm)



4-gang* CW-4-<u>CC</u>² SC-4-**CC**⁴

W: 8.37 in (213 mm); H: 4.69 in (119 mm);


D: .30 in (7.6 mm)



2-gang* CW-2-**CC**² SC-2-**CC**⁴

W: 4.75 in (121 mm); H: 4.69 in (119 mm);

D: .30 in (7.6 mm)




5-gang* CW-5-<u>CC</u>² SC-5-**CC**⁴

W: 10.18 in (259 mm); H: 4.69 in (119 mm);

D: .30 in (7.6 mm)

Multiple devices with line and low-voltage can be mounted behind a common wallplate using a standard barrier backbox, see Application Note #213 (Combining Low-Voltage and Line Voltage Wiring Devices in a Multi-Gang Box) at www.lutron.com/applicationnotes.



3-gang* CW-3-<u>CC</u>² SC-3-**CC**⁴

W: 6.56in (167 mm); H: 4.69in (119 mm);


D: .30 in (7.6 mm)

<u>CC</u>²: Gloss and Stainless Steel color codes, see pg. 161

CC⁴: Satin color codes, see pg. 161

Multi-gang dimmer installations may require derating, see pg. 170.

*Stainless Steel finish wallplates include black plastic trim/adapter, visible from side. Match with separate Black (BL) or Midnight (MN) controls and accessories.



6-gang* CW-6-<u>CC</u>² SC-6-**CC**⁴

W: 12.00 in (305 mm); H: 4.69 in (119 mm);

D: .30 in (7.6 mm)

Cable jacks



F-style, 75-Ohm coaxial cable

Single cable jack*	CA-CJH- <u>CC</u> 3
	SC-CJ- <u>CC</u> ⁴

Telephone jacks



6-conductor telephone jack, RJ11

Single telephone jack* CA-PJH-<u>CC</u>³ SC-PJ-**CC**⁴

CC²: Gloss and Stainless Steel color codes, see pg. 161

<u>CC</u>³: Gloss color codes, see pg. 161

CC⁴: Satin color codes, see pg. 161

Receptacles



Tamper resistant receptacles

15A, 125V*	CARS-15-TR- <u>CC</u> ³
	SCRS-15-TR- <u>CC</u> 4
20A, 125V*	SCRS-20-TR- <u>CC</u> ⁴

Receptacles

·	
15A, 125V*	CAR-15H- <u>CC</u> 3
	SCR-15- <u>CC</u> ⁴
20A, 125V*	SCR-20- <u>CC</u> ⁴

GFCI Receptacles



- Press test button to confirm LED indicator status
- Press reset button to reset GFCI after circuit interruption

Tamper resistant GFCI receptacles

•	•	
15A, 125V*	GFCI	CAR-15-GFTR- CC ³
		SCR-15-GFTR- CC ⁴
20A, 125V*	GFCI	SCR-20-GFTR- <u>CC</u> ⁴

Receptacles for dimming use



- Duplex for dimming both connected loads
- Projecting nubs prevent standard plugs from being used
- Requires replacement plugs for dimming use

Duplex for dimming use

15A	120/125V*	CAR-15-DFDU- <u>CC</u> ²
15A	120/125 V*	SCR-15-DFDU- <u>CC</u> 4
20 A	120/125V*	CAR-20-DFDU- <u>CC</u> ²
20A	120/125 V*	SCR-20-DFDU- <u>CC</u> 4

Receptacles for dimming use



- Top half for dimming
- Projecting nub prevents standard plug from being used
- Requires replacement plugs for dimming use
- Bottom half is a general use receptacle and will fit standard duplex plugs

Split duplex (half for dimming use)

15A	120/125V*	CAR-15-HFDU- <u>CC</u> 2
15A	120/125V*	SCR-15-HFDU- <u>CC</u> ⁴
20A	120/125V*	CAR-20-HFDU- <u>CC</u> ²
20 A	120/125V*	SCR-20-HFDU- <u>CC</u> ⁴

Receptacles for dimming use



- Duplex for dimming both connected loads
- Projecting nubs prevent standard plugs from being used
- Requires replacement plugs for dimming use
- 15A model shown
- Tamper resistant shutter mechanism

Dual dimming tamper resistant

15A	120/125V*	CAR-15-DDTR- <u>CC</u> ²
15A	120/125V*	SCR-15-DDTR- <u>CC</u> ⁴
20A	120/125V*	CAR-20-DDTR- CC ²
20 A	120/125 V*	SCR-20-DDTR-CC

Receptacles for dimming use



- Top half for dimming
- Projecting nub prevents standard plug from being used
- Requires replacement plugs for dimming use
- Bottom half is a general use receptacle and will fit standard duplex plugs
- 15A model shown
- Tamper resistant shutter mechanism

Half dimming tamper resistant

15A	120/125V*	CAR-15-HDTR- <u>CC</u> ²
15A	120/125V*	SCR-15-HDTR- <u>CC</u> ⁴
20A	120/125V*	CAR-20-HDTR- <u>CC</u> 2
20A	120/125V*	SCR-20-HDTR- <u>CC</u> ⁴

CC²: Gloss color code and Stainless Steel,

see pg. 161

CC⁴: Satin color codes, see pg. 161

Replacement plug for dimming (use with receptacles on left)



- This plug required for use with Lutron® receptacles for dimming use—plug will work in standard receptacle
- Easily replaces the existing plugs on lamps

120/125V	RP-FDU-10-WH
White	
120/125V	RP-FDU-10-BR
Brown	

UL/CSA/NOM regulatory approvals.

Important notes

- If the hot and dimmed hot feeds to the split duplex HFDU are supplied from different circuits or split-wired with separate switch-legs, a means to simultaneously disconnect these circuits must be provided at the panel board where they originate (NEC 210.7(C) 2002 Edition). A 2-pole circuit breaker or two single-pole circuit breakers with an approved handle tie can be used to accomplish this simultaneous disconnect. Feed-through dimming panels, which are those without breakers, are recommended when using the HFDU.
- Receptacles and plugs for dimming use are UL listed for use with all Lutron® wallbox dimmers included in this catalog.
- If there is only one electrical feed to the receptacle, then the duplex DFDU must be used.
- For detailed information, see Application Notes #91 (Guide to Dimming Table Lamps) and #109 (Guide to Dimming Portable Lamps via Receptacles) at www.lutron.com/applicationnotes.

CC²: Gloss color code and Stainless Steel, see pg. 161

CC4: Satin color codes, see pg. 161

Field customizable 6-port frame



- Shipped with six blanks in matching colors
- Connectors and wallplate sold separately
- Connectors snap in (no tools required)
- Connectors available in White (WH), unless noted

6-port frame*	CA-6PF- <u>CC</u> ³
	SC-6PF- <u>CC</u>⁴

Connectors for 6-port frame

Telephone/network jacks



8-conductor,	CON-1P-C3- EE ⁴
RJ45 category 3	
8-conductor,	CON-1P-C5E- EE⁴
RJ45 category 5e	
8-conductor,	CON-1P-C6- EE⁴
RJ45 category 6	

Fiber jacks



CON-1F-MTRJ-WH
CON-1F-SC-WH
CON-1F-LC-WH
CON-1F-ST-WH

Cable jack



F-style,	CON-1C- <u>EE⁴</u>
75-Ohm coaxial cable	

BNC jack



BNC connector, 50-Ohm	CON-1B-WH

Connectors only for use with 6-port frame.

Switches



- · Paddle turns on/off
- · Use with any 15A load
- General purpose switching of all sources and motor loads
- · No derating if ganged

General purpose switches (120/277 V)

CA-1PSH- CC ³
5
SC-1PS- <u>CC</u> ⁴
CA-3PSH- <u>CC</u> 3
SC-3PS- <u>CC</u> ⁴
CA-4PSH- CC ³
SC-4PS- <u>CC</u> ⁴

General purpose switch with locator light (120 V only)

Single-pole	15A*	CA-1PSNL- EE ²
		SC-1PSNL- <u>EE</u> 10
3-way	15A*	CA-3PSNL- EE 2
		SC-3PSNL- <u>EE</u> 10
4-way	15A*	CA-4PSNL- <u>EE</u> 2
		SC-4PSNL- <u>EE</u> 10

CC³: Gloss color codes, see pg. 161

CC⁴: Satin color codes, see pg. 161

EE²: Only available in Almond (AL), Ivory (IV), Light Almond (LA) and White (WH)

<u>EE</u>⁴: Only available in White (WH) and Black (BL)

EE¹⁰: Available in Biscuit (BI), Eggshell (ES), Goldstone (GS), Limestone (LS), Sea Glass (SG) and Snow (SW)

How to understand ganging and derating

Standard ganging

Ganging is the side-by-side mounting of two or more dimmers or accessory devices under a multi-gang wallplate.

Standard multi-gang installation:


- Uses standard multi-gang electrical backboxes
- · Uses standard multi-gang wallplates
- Requires fins to be removed from dimmers for proper spacing ("Fins Broken" ganging)
- May require derating (i.e., reduction of dimmer capacity due to fin removal), see Derating Tables, pgs. 172–173

Custom ganging for Architectural style controls

For Architectural style dimmers and switches, it is possible to retain the maximum capacity of dimmers in multi-gang applications via custom architectural multi-gang:

- May require customized, wider-thanstandard wallplates
- May require wider-than-standard electrical backboxes
- · Allows full capacity ("No Fins Broken") ganging
- Required for Nova® dimmers and for larger width (high capacity) architectural controls
- Visit www.lutron.com/customganging for additional information

Standard ganging for dimmers, switches and accessories



Standard ganging and fins broken derating examples:



One Nova T☆® dimmer



No fins broken Full capacity



Standard 1-gang backbox



Standard 1-gang architectural wallplate



Two Nova T☆ dimmers "Fins Broken" ganging




One fin broken* Partial derating




Standard 2-gang backbox



Standard 2-gang architectural wallplate




Three Nova T☆ dimmers "Fins Broken" ganging




Inside: Two fins broken*
Full derating

Outside: One fin broken*



Standard 3-gang backbox



Standard 3-gang architectural wallplate

Custom Architectural ganging example:



Two Nova T☆ dimmers "No Fins Broken" ganging




Partial derating

No fins broken Full capacity



Backbox with chase nipple



Custom architectural wallplate

For further information on ganging and derating, visit www.lutron.com/multigang.

*The fins are scored and designed to be removed easily.

Appendix | Ganging and derating

Derating Table 1

New Architectural | Vierti®

Designer | Maestro®, Maestro IR®, Maestro Wireless®, Spacer System®, Diva®, Lyneo® Lx, Skylark Contour™, Skylark® **Traditional** | Abella®, Ceana®, Ariadni®, Glyder®, Rotary

	No fins broken	1 fin broken	ূ্ৰ 2 fins broken
Incandescent			
Dimmers	600W	500W	400 W
	1000W	800W	650W
Dual dimmers	300W	250W	200 W
	300W	250W	200 W
Magnetic low-voltage			
Dimmers	600 VA / 450 W	500 VA / 400 W	400 VA/300 W
	1000 VA/800 W	800 VA / 650 W	650 VA/500 W
Electronic low-voltage			
Dimmers	300W	250W	200 W
	500 W	450W	400 W
	600 W	500 W	400 W
Fluorescent			
Hi-lume _® /Hi-lume _® Compact SE/Eco-10 _® /	EcoSystem _®		
Vierti	60 ballasts/6A	50 ballasts/5A	35 ballasts/3.5A
Maestro/Spacer System	20 ballasts/6A	20 ballasts/5A	20 ballasts/3.5A
Diva, Skylark, Lyneo Lx and Ariadni	no derating	no derating	no derating
Tu-Wire®: Spacer System, Diva, Skylark	5A	4A	3.3A
Fan controls			
Quiet 7-speed	1.0A/300W	1.0A/300W	1.0A/300W
Quiet 3-speed	1.5A	1.5A	1.5A
Fully variable	5A	4A	3A
Fan/light controls			
Quiet 7-speed	1.0A/300W	1.0A/300W	1.0A/300W
Quiet 3-speed	1.5A/300W	1.5A/300W	1.5A/300W
	1.5A/360W	1.5A/360W	1.5A/360W
Fully variable	2.5A/300W	2.1A/250W	1.7A/200W
Electronic switches			
Vierti	6A/3A	5A/3A	3.5A/3A
Maestro (light/fan)	8A/3A	6.5A/3A	5A/3A
Abella (light/fan)	6A/3A	5A/3A	3.5A/3A

Appendix | Ganging and derating

Derating Table 2

Architectural | Vareo®, Nova T☆®

	শূরী No fins broken	្រី 1 fin broken	2 fins broken
Incandescent			
Dimmers	600 W	500W	300W
	1000W	900W	700W
	1500W	1250W	1000W
	1950W	_	_
Magnetic low-voltage	·	^	
Dimmers	600 VA / 450 W	500 VA /400 W	300 VA/250 W
	1000 VA/800 W	900 VA / 750 W	700 VA/500 W
	1500 VA/1200 W	1250 VA / 1000 W	1000 VA/800 W
Electronic low-voltage			
Dimmers	300W	300W	250W
	600 W	500W	400 W
Fluorescent	·	^	
Hi-lume _® /Hi-lume _® Compact SE/	Eco-10⊛/EcoSystem®		
Vareo	20 ballasts/8A	20 ballasts/6A	20 ballasts/4.5 A
Nova T☆	6A	no derating	no derating
	8A	no derating	no derating
	16A	no derating	no derating
0-10 VDC control ¹	30 mA ballasts	no derating	no derating
Tu-Wire®	5A	4A	3.3A
Fan controls			
Quiet 3-speed	1.5A	no derating	no derating
Fully variable	6A	4.2 A	2.5 A
Fully variable	12A	10A	8.3A
Electronic tapswitches ²			
VETS-1000-	1000W	800W	650W
VETS-1000-SL-	1000W	900 W	700 W
VETN-1000-	1000 VA	700 VA	550 VA

For further information on ganging Nova®, visit www.lutron.com/customganging.

¹PowerPack required for line voltage switching.

²VETS-R-Auxiliary electronic tapswitches do not require derating.

Dimmer capabilities and interface requirements

Multi-location—true dimming from each location

eco-model available

Compatible dimmer (no interface)

WBX TVI 3F PA Requires interface, see notes below



Dimmers	capacity [†]	0				
	600 W			W		
	1000 W			O		
	1500W		WBX			
	2000 W		WBX			
Magnetic low-voltage 120V	600 VA (450 W)					
	1000 VA (800 W)					
	1500 VA (1200 W)		WBX			
	2000 VA (1600 W)		WBX	WBX		
▼ Magnetic low-voltage 277∨	600 VA (450 W)		WBX		WBX	
	1000 VA (800 W)		WBX		WBX	
₩ Electronic low-voltage 120V	300W		WBX			
	450W		WBX	WBX		
	600W		WBX		WBX	
₩ Electronic low-voltage 277 V	16A		WBX	WBX	WBX	
Neon/cold cathode			WBX	WBX		
ঞ্®3-wire ballasts and Hi-lume⊚ LE	ED driver 120V 6A					
Hi-lume, Hi-lume Compact SE,	8A					
Eco-10 _® and EcoSystem _® ballasts	16A		3F			
य•⁄ ®3-wire ballasts and Hi-lume LED driver 277			3F			
Hi-lume, Hi-lume Compact SE,	8A		3F			
Eco-10 and EcoSystem ballasts	16A		3F	3F	3F	
ℤ⊭ Tu-Wire ballasts 120V	5A		PA			
☞⊚0-10 VDC (ballasts or LED Drivers) 120/277V 16A	TVI	TVI			

WBX: Wallbox Phase Adaptive Power Module

(PHPM-WBX-DV-WH)

3F: Fluorescent Power Module

(PHPM-3F-DV-WH)

TVI: 0-10 V Interface

(GRX-TVI)

PA: Phase Adaptive Power Module

(PHPM-PA-DV-WH)

See pgs. 178–179 for specific compatible dimmer models and switching interface solutions.

*Consult Lutron Technical Support for information on interfaces with Vierti.

[†]UL listed for FULL wattage indicated (derate capacity only if ganged with other devices).

Dimmer capabilities and interface requirements

Multi-location—true dimming from each location

eco-model available

Compatible dimmer (no interface)

WBX TVI 3F PA Requires interface, see notes below



capacity [†]	Ø	Ø	0	Ø	
600 W	(3				3
1000W					
1500W	WBX		WBX	WBX	WBX
2000W	WBX		WBX	WBX	WBX
600 VA (450 W)					
1000 VA (800 W)					
1500 VA (1200 W)	WBX		WBX	WBX	WBX
2000 VA (1600 W)	WBX		WBX	WBX	WBX
600 VA (450 W)	WBX		WBX	WBX	WBX
1000 VA (800 W)	WBX		WBX	WBX	WBX
300W			WBX		
450W			WBX		WBX
600W			WBX		WBX
16A	WBX		WBX	WBX	WBX
			WBX		WBX
D driver 120V 6A					
8A	3F		3F	3F	
16A	3F		3F	3F	3F
driver 277V 6A					
8A	3F		3F	3F	3F
16A	3F		3F	3F	3F
5A	PA		PA		
0-10VDC (ballasts or LED Drivers) 120/277 V 16A			TVI	TVI	TVI
	600 W 1000 W 1500 W 2000 W 600 VA (450 W) 1000 VA (800 W) 1500 VA (1200 W) 2000 VA (1600 W) 600 VA (450 W) 1000 VA (800 W) 300 W 450 W 600 W 16 A D driver 120 V 6 A 8 A 16 A 0 driver 277 V 6 A 8 A 16 A 5 A	600W 1000W 1500W WBX 2000W WBX 600VA (450W) 1000VA (800W) 1500VA (1200W) WBX 2000VA (1600W) WBX 600VA (450W) WBX 1000VA (800W) WBX 300W 450W 600W 16A WBX D driver 120V 6A 8A 3F 16A 3F 16A 3F 16A 3F 16A 3F 16A 3F	600W 1000W 1500W WBX 2000W WBX 600VA (450W) 1000VA (800W) 1500VA (1200W) WBX 2000VA (1600W) WBX 600VA (450W) WBX 300W 450W 600W 16A WBX D driver 120V 6A 8A 3F 16A 3F 16A 3F 16A 3F 16A 3F 16A 3F 16A 3F	600 W 1000 W WBX WBX 2000 W WBX WBX 2000 W WBX WBX 600 VA (450 W) 1500 VA (1200 W) 2000 VA (1600 W) WBX WBX 600 VA (450 W) WBX WBX 600 VA (450 W) WBX WBX WBX 1000 VA (800 W) WBX WBX WBX 300 W WBX WBX 450 W WBX MBX D driver 120 V 6 A 8 A 3F 3F 16 A 3F 3F	600W 1000W 1500W WBX WBX WBX WBX 2000W WBX WBX WBX WBX WBX WBX WBX WBX WBX WB

WBX: Wallbox Phase Adaptive Power Module

(PHPM-WBX-DV-WH)

3F: Fluorescent Power Module

(PHPM-3F-DV-WH)

TVI: 0-10 V Interface

(GRX-TVI)

PA: Phase Adaptive Power Module

(PHPM-PA-DV-WH)

See pgs. 178–179 for specific compatible dimmer models and switching interface solutions.

†UL listed for FULL wattage indicated (derate capacity only if ganged with other devices).

Dimmer capabilities and interface requirements

Multi-location—true dimming from each location

eco-model available

Compatible dimmer (no interface)

WBX TVI 3F PA Requires interface, see notes below



			pg. 100		
Dimmers	capacity [†]				W
	600 W		•	•	
	1000 W				
	1500 W	WBX		WBX	
	2000 W	WBX		WBX	
▼ Magnetic low-voltage 120V	600 VA (450 W)				
	1000 VA (800 W)			WBX	
	1500 VA (1200 W)	WBX		WBX	
	2000 VA (1600 W)	WBX		WBX	
▼ Magnetic low-voltage 277 ∨	600 VA (450 W)	WBX		WBX	
	1000 VA (800 W)	WBX		WBX	
₩ Electronic low-voltage 120 V	300 W				
	450W			WBX	
	600W			WBX	
ਓ Electronic low-voltage 277 V	16A	WBX		WBX	
_ Neon/cold cathode		WBX		WBX	
್ರಾ⊛3-wire ballasts and Hi-lume⊚ LE	D driver 120V 6A				
Hi-lume, Hi-lume Compact SE,	8A				
Eco-10 _® and EcoSystem _® ballasts	16A	3F		3F	
್ರಾ⊚3-wire ballasts and Hi-lume LEI					
Hi-lume, Hi-lume Compact SE,	8A	3F		3F	
Eco-10 and EcoSystem ballasts	16A	3F		3F	
∠-Tu-Wire ballasts 120 V	5A	PA			
☞ 0-10 VDC (ballasts or LED Drivers	120/277V 16A	TVI		TVI	

WBX: Wallbox Phase Adaptive Power Module

(PHPM-WBX-DV-WH)

3F: Fluorescent Power Module

(PHPM-3F-DV-WH)

TVI: 0-10 V Interface

(GRX-TVI)

PA: Phase Adaptive Power Module

(PHPM-PA-DV-WH)

See pgs. 178–179 for specific compatible dimmer models and switching interface solutions.

†UL listed for FULL wattage indicated (derate capacity only if ganged with other devices).

Dimmer capabilities and interface requirements

Multi-location—true dimming from each location

eco-model available

Compatible dimmer (no interface)

WBX TVI 3F PA Requires interface, see notes below



Dimmers	capacity [†]		
☐ Incandescent/halogen 120V	600 W	9	a
	1000 W		
	1500W	WBX	
	2000 W	WBX	
∀ Magnetic low-voltage 120 V	600 VA (450 W)		
	1000 VA (800 W)		
	1500 VA (1200 W)	WBX	
	2000 VA (1600 W)	WBX	
▼ Magnetic low-voltage 277 V	600 VA (450 W)	WBX	
	1000 VA (800 W)	WBX	
ਓ Electronic low-voltage 120 V	300W	WBX	
	450W	WBX	
	600W	WBX	
₩ Electronic low-voltage 277 V	16A	WBX	
_ Neon/cold cathode		WBX	
ಾ್®3-wire ballasts and Hi-lume® LE	D driver 120V 6A		
Hi-lume, Hi-lume Compact SE,	8A		
Eco-10 _® and EcoSystem _® ballasts	16A	3F	
್ರಾ⊛3-wire ballasts and Hi-lume LEI	Odriver 277 V 6A		
Hi-lume, Hi-lume Compact SE,	8A	3F	
Eco-10 and EcoSystem ballasts	16A	3F	
Z: Tu-Wire	5A	PA	
☞/◎0-10VDC (ballasts or LED Drivers)	120/277V 16A	TVI	

WBX: Wallbox Phase Adaptive Power Module

(PHPM-WBX-DV-WH)

3F: Fluorescent Power Module

(PHPM-3F-DV-WH)

TVI: 0-10V Interface

(GRX-TVI)

PA: Phase Adaptive Power Module

(PHPM-PA-DV-WH)

See pgs. 178–179 for specific compatible dimmer models and switching interface solutions.

†UL listed for FULL wattage indicated (derate capacity only if ganged with other devices).

Dimmer models/load interface compatibility

	Incandescent, magnetic and electronic low-voltage (120/277 V)		and electronic ballasts or Hi-lume⊚		0-10 VDC Ballasts or LED drivers (120/277 V)	
	WBX		3F		TVI	
	Wallbox Phas Power Modul	le*	Fluorescent Power Modu		0-10 V Interface	
	PHPM-WBX-	-DV-WH	PHPM-3F-D)V-WH	GRX-TVI	
Dimmer Family	Single- pole	3-way or multi-location	Single- pole	3-way or multi-location	Single- pole	3-way or multi-location
Abella®	_	_	_	_	_	_
Ariadni®	_	AYF-103P-	_	AYF-103P-	_	AYF-103P-
Ceana®	_	_	_	_	_	_
Diva _® Gloss	_	DVF-103P-	_	DVF-103P-	-	DVF-103P-
Diva Satin Colors®	_	DVSCF- 103P-	_	DVSCF- 103P-	_	DVSCF- 103P-
Glyder _®	_	_	_	_	_	_
Lyneo _® Lx	_	LXF-103PL-	_	LXF-103PL-	_	LXF-103PL-
Maestro® Gloss	_	MAF-6AM-	_	MAF-6AM-	_	MAF-6AM-
Maestro® Satin Colors®	_	MSCF-6AM-	_	MSCF-6AM-	_	MSCF-6AM-
Maestro Wireless®	_	MRF2- F6AN-DV-	_	MRF2- F6AN-DV-	_	MRF2- F6AN-DV-
Nova®	NF-10-	NF-103P-	NF-10-	NF-103P-	NF-10-	NF-103P-
Nova T☆®	NTF-10-	NTF-103P-	NTF-10-	NTF-103P-	NTF-10-	NTF-103P-
Skylark _®	SF-10P-	SF-103P-	SF-10P-	SF-103P-	SF-10P-	SF-103P-
Spacer System®	_	SPSF-6AM-	_	SPSF-6AM-	SPSF-S6A-	SPSF-6AM-
Vareo®	_	VF-10-	_	VF-10-	_	VF-10-
Vierti®	conta	ct Lutron	conta	act Lutron	_	VTF-6AM-

Use only dimmer model numbers listed.

^{*}Dual 120/277 V model given,120 V only versions are also available. Please see Technical notes, pg. 179.

Dimmer models/load interface compatibility

	Tu-Wire⊚ Fluorescent Ballasts (120V)		Switched (120/277 V)	
	PA		sw	
	Phase Ada Power Mo PHPM-PA	dule*	Switching Power Mod PHPM-SW	
Dimmer Family	Single- pole	3-way or multi-location	Single- pole	3-way or multi-location
Abella®	_	_	_	AB-S6AM-
Ariadni®	_	AYF-103P-	_	_
Ceana®	_	_	_	_
Diva _® Gloss	_	DVF-103P-	_	_
Diva Satin Colors®	-	DVSCF-103P-	-	_
Glyder®	_	_	_	_
Lyneo _® Lx	_	LXF-103PL-	LX-1PSL-	LX-3PSL-
Maestro _® Gloss	_	MAF-6AM-	_	MA-S8AM-
Maestro® Satin Colors®	_	MSCF-6AM-	_	MSC-S8AM-
Maestro Wireless®	_	MRF2- F6AN-DV-	_	MRF2-6ANS-
Nova®	NF-10-	NF-103P-	_	_
Nova T☆®	NTF-10-	NTF-103P-	_	_
Skylark _®	SF-10P-	SF-103P-	_	_
Spacer System _®	SPSF- S6A-	SPSF-6AM-	SPSF- S6A-	SPSF-S6AM-
Vareo _®	_	VF-10-	_	VETN-1000-
Vierti®	cont	act Lutron	cont	act Lutron

Technical notes

- Lighting load interfaces must be matched to load type and voltage
- All load interfaces for dimmed load are controlled by a 120 V 3-wire fluorescent dimmer
- Power feed to dimmer may differ from lighting load/interface voltage
- Interfaces typically require additional power feeds
- For wiring information, consult wiring diagrams, see pgs. 193-195
- For assistance and additional solutions, consult Lutron Technical Support at 1.800.523.9466 (24 hours/7 days)


Interface mounting

- PHPM interfaces mount to 2-gang electrical backbox (W: 6.30 in x H: 5.10 in)
- GRX-TVI enclosure is surface mount only (W: 6.10 in x H: 12.50 in x D: 3.30 in)

Use only dimmer model numbers listed.

*Dual 120/277 V model given, 120 V only versions are also available. Please see Technical notes, pg. 179.

Skylark Contour™



For illustration purposes only. Consult model number pages for specific voltage and capacity information.

www.lutron.com | 1.800.523.9466 | **LUTRON**.

2.94 in (75 mm)



Shown actual size: Skylark dimmer and 1-gang Claro wallplate in White (WH).

Product family features

- Rocker switch returns light to your favorite light level
- Slide up to brighten, down to dim (adjust light to suit any activity)
- · eco-dim_® model available
- 1000W preset dimmers have voltage compensation which maintains stable light levels, despite line voltage variations
- · 100% factory tested
- Coordinating Claro® and Stainless Steel wallplates only available separately
- Custom engraving available for wallplates, see pg. 155

Control types

Single-pole (one location)

a-way or 4-way (two or more locations)

Direct load type compatibility

- ▼ Magnetic low-voltage lighting
- ☐ Electronic low-voltage lighting
- LED lighting
- Dimmable compact fluorescent
- Ceiling fans
- ★ Ceiling fan/lights

Load type requiring load interface

Neon/cold cathode lighting

Lighting load interfaces may be applicable for some additional load type, voltage and capacity combinations.

For additional information, see pg. 174.

Available finishes

Use **BOLD** color code in model number (Example: S-600P-**GR**) Gloss finishes*



^{*}Coordinating wallplates only available separately. For wallplate information, see pg. 160.

Stainless Steel wallplate includes black plastic trim/adapter, visible from side. Match with separate Black (BL) controls.

Dimmers

Slide-to-off dimmers



 Slide up to on/brighten; down to dim/off

Dimmers with on/off switch and locator light



- · Rocker switch turns on/off
- Slide up to brighten; down to dim
- · Includes amber locator light

Dimmers with on/off switch



- · Rocker switch turns on/off
- Slide up to brighten; down to dim
- eco-dim_® model guarantees at least 15% energy savings compared to a standard switch

Skylark_® dimmers and fan controls

Fan and fan/light controls

Slide-to-off fan controls



- · Slide up to on/increase speed; down to decrease/off
- 3-quiet fan speeds for increased comfort
- · For use with only one ceiling paddle fan
- · Quiet 3-speed designed to prevent motor hum
- Fully variable model also available

Dual devices

Dual slide-to-off dimmers (two loads)



Dimmers (left/right)

 Slide up to on/brighten; down to dim/off

Slide-to-off fan controls with on/off light switch



Fan control (top)

- · Slide up to on/increase fan speed; down to decrease fan speed/off
- 3-quiet fan speeds for increased comfort
- · For use with only one ceiling paddle fan
- · Quiet 3-speed designed to prevent motor hum

Switch (bottom)

· Rocker switch turns light on/off

Dual slide-to-off fan control and dimmer



Fan control (left)


- · Slide up to on/increase speed; down to decrease/off
- 3-quiet fan speeds for increased comfort
- Quiet 3-speed designed to prevent motor hum
- Fully variable available for use with multiple paddle or exhaust fans

Dimmer (right)

· Slide up to on/brighten; down to dim/off


Connections overview

Load connections*



Control types (for 2 or more locations)

Dim from one location, switch from the others



For more information on ballasts, visit **www.lutron.com/ballasts**. For more information on LED drivers, visit **www.lutron.com/LED**.

*For illustration purposes only. Consult model number pages for specific voltage and capacity information.

Dimmer model numbers

Dimmers with on/off switch

Single-pole	S-600P- <u>CC</u> ³
120V 600W	
Single-pole	S-10P- <u>CC</u> 3
120V 1000W	
3-way	S-603P- <u>CC</u> ³
120V 600W	
3-way	S-103P- <u>CC</u> 3
120V 1000W	

eco-dime dimmer with on/off switch

3-way/single-pole	S-603PG- EE 2
120V 600W	

eco-dim model guarantees at least 15% energy savings compared to a standard switch.

Dimmers with on/off switch and locator light

Single-pole	S-600PNL- <u>CC</u> 3
120V 600W	
Single-pole	S-10PNL- <u>CC</u> 3
120V 1000W	
3-way	S-603PNL- <u>CC</u> 3
120V 600W	
3-way	S-103PNL- <u>CC</u> 3
120V 1000W	

Slide-to-off dimmers

Single-pole	S-600- CC 3
120V 600W	
Single-pole	S-1000- <u>CC</u> ³
120V 1000W	

For dual slide-to-off dimmers (two loads), see page 111.

▼ Magnetic low-voltage dimmers

Dimmers with on/off switch

Single-pole	SLV-600P- CC 3
120V 600VA (450W)	
3-way	SLV-603P- CC 3
120V 600VA (450W)	

The stated VA (Volt-Ampere) rating includes the magnetic transformer heat losses and the lamp load. The stated W (Watt) rating is the maximum lamp wattage based on assumed 20% transformer loss.

□ Electronic low-voltage dimmers*

Dimmers with on/off switch

Single-pole	SELV-300P- <u>CC</u> 3
120V 300W	
3-way	SELV-303P- CC ³
120V 300W	
•	

Certain LED drivers are dimmable using an ELV dimmer, for more information, visit www.lutron.com/LED.

CC³: Gloss color codes, see pg. 105

EE²: Available in White (WH), Ivory (IV), Almond (AL) and Light Almond (LA) (Wallplates not included, order separately, see pg. 160)

All models must be derated if ganged unless otherwise noted, see pg. 170.

Dimmer model numbers

Z 3-wire fluorescent dimmers*

Dimmers with on/off switch

Single-pole	SF-10P- <u>CC</u> ³
120V 8A	
Single-pole	SF-12P-277- CC 3
277V 6A	
3-way	SF-103P- <u>CC</u> ³
120V 8A	
3-way	SF-12P-277-3- <u>CC</u> 3
277V 6A	

For use with Hi-lume®, Hi-lume® Compact SE, Hi-lume® 3D, Eco-10®, EcoSystem® ballasts.

No derating required if ganged.

Adjustable low-end trim.

Dimmers with on/off switch

Single-pole	SF-10P- CC ³
120V 8A	
Single-pole	SF-12P-277- <u>CC</u> 3
277V 6A	
3-way	SF-103P- <u>CC</u> ³
120V 8A	
3-way	SF-12P-277-3- <u>CC</u> 3
277V 6A	

For use with Hi-lume LED driver only.

For more information on Hi-lume LED drivers, visit **www.lutron.com/HilumeLED**.

No derating required if ganged.

Adjustable low-end trim.

☐ Tu-Wire® fluorescent dimmers

Dimmers with on/off switch

3-way/single-pole	SFTU-5A3P- <u>CC</u> 3	
120V 5A		
Also compatible with Advance Mark X		

ballasts, for further information, visit

www.lutron.com/advance.

For information on use with Universal and OSRAM ballasts, contact Technical Support at 1.800.523.9466.

CC³: Gloss color codes, see pg. 105 (Wallplates not included, order separately, see pg. 160)

For more information on ballasts, visit www.lutron.com/ballasts.

All models must be derated if ganged unless otherwise noted, see pg. 170.

Fan control model numbers

★ Fan controls

Slide-to-off fan controls—quiet 3-speed

Single-pole SFSQ-F-CC3 120V 1.5A Single-pole SFSQ-F-HO-CC³

120V 2.0A

For use with only one ceiling paddle fan.

SFSQ-F-HO- for use with Hunter Original Series.

Slide-to-off fan control—fully variable

SFS-5E-CC3 Single-pole 120V 5A

For use with multiple ceiling paddle fans or exhaust fans.

Fan/light controls

Fan control—quiet 3-speed and dimmer

Single-pole fan control S2-LFSQ-CC³ 120V 1.5A (left)

120V single-pole dimmer 300W (right)

For use with only one ceiling paddle fan.

Fan control—fully variable and dimmer

Single-pole fan control S2-LF-**CC**3

120V 2.5A (left)

120V single-pole dimmer 300W (right)

For use with multiple ceiling paddle fans.

Fan control/light switch

Fan control—quiet 3-speed and switch

SFSQ-LF-CC³ Single-pole fan control 120V 1.5A (top) 120V single-pole switch 360W (bottom) (incandescent/halogen loads only)

CC³: Gloss color codes, see pg. 105 (Wallplates not included, order separately, see pg. 160)

All models must be derated if ganged unless otherwise noted, see pg. 170.

Dual device model numbers

√ Incandescent/halogen and Incandescent/halogen dimmers

Dual slide-to-off dimmers (two loads)

Single-pole S2-L-**CC**³
120V 300W light (left)
incandescent/halogen
120V 300W light (right)
incandescent/halogen

Replacement knob model numbers

Knobs

Single-pole	SK- <u>EE</u> ²
Standard knob	
Split knobs	contact customer service

CC³: Gloss color codes, see pg. 105 (Wallplates not included, order separately, see pg. 160)


EE²: Available in White (WH), Ivory (IV), Almond (AL) and Light Almond (LA)

All models must be derated if ganged unless otherwise noted, see pg. 170.

Accessories

Wallplates


4.75 in (121 mm)



Shown actual size: 2-gang Claro® wallplate in White (WH). For more information about Designer wallplates, see pg. 160.

Coordinated electrical devices








For more information about coordinated Designer electrical devices, see pg. 163.

6-port frame

Wallplates and accessories | Designer | Claro / Satin Colors



Product family features

- Can be used in conjunction with the following dimmer(s) and switch(es):
 Maestro®, Maestro IR®, Maestro Wireless®,
 Pico™ wireless control, Spacer System®,
 Diva®, Lyneo® Lx, Skylark®, Skylark Contour™
- All Lutron® wallplates are screwless, seamless and have no visible hardware; the front plate securely snaps into the alignment adapter plate
- Full line of wiring devices in designer style opening
- Blank inserts available for Gloss colors (DV-BI-) and Satin colors (SC-BI-)
- Customize your designer wallplate with engraving, contact customer service to get started at 1.888.LUTRON1

Ganging and derating

- · Designer wallplates use standard ganging
- Requires fins to be removed from dimmers for proper spacing ("Fins Broken" ganging), see pg. 170
- May require derating (i.e., reduction of dimmer capacity due to fin removal), see Derating Tables, pg. 172

Available finishes

Use ${f BOLD}$ color code in model number (Example: SC-1- ${f PL}$)

Gloss finishes



Satin finishes



^{*}Stainless Steel finish wallplates include black plastic trim/adapter, visible from side. Match with separate Black (BL) or Midnight (MN) controls and accessories.

Wallplates for Maestro®, Maestro IR®, Maestro Wireless®, Pico™ wireless control, Spacer System®, Diva®, Lyneo® Lx, Skylark® and Skylark Contour™




1-gang*

CW-1-<u>**CC**</u>² SC-1-<u>**CC**⁴</u>

W: 2.94 in (75 mm); H: 4.69 in (119 mm)


D: .30 in (7.6 mm)



4-gang* CW-4-<u>CC</u>² SC-4-**CC**⁴

W: 8.37 in (213 mm); H: 4.69 in (119 mm);


D: .30 in (7.6 mm)



2-gang* CW-2-**CC**² SC-2-**CC**⁴

W: 4.75 in (121 mm); H: 4.69 in (119 mm);

D: .30 in (7.6 mm)




5-gang* CW-5-<u>CC</u>² SC-5-**CC**⁴

W: 10.18 in (259 mm); H: 4.69 in (119 mm);

D: .30 in (7.6 mm)

Multiple devices with line and low-voltage can be mounted behind a common wallplate using a standard barrier backbox, see Application Note #213 (Combining Low-Voltage and Line Voltage Wiring Devices in a Multi-Gang Box) at www.lutron.com/applicationnotes.



3-gang* CW-3-<u>CC</u>² SC-3-**CC**⁴

W: 6.56in (167 mm); H: 4.69in (119 mm);


D: .30 in (7.6 mm)

<u>CC</u>²: Gloss and Stainless Steel color codes, see pg. 161

CC⁴: Satin color codes, see pg. 161

Multi-gang dimmer installations may require derating, see pg. 170.

*Stainless Steel finish wallplates include black plastic trim/adapter, visible from side. Match with separate Black (BL) or Midnight (MN) controls and accessories.



6-gang* CW-6-<u>CC</u>² SC-6-**CC**⁴

W: 12.00 in (305 mm); H: 4.69 in (119 mm);

D: .30 in (7.6 mm)

Cable jacks



F-style, 75-Ohm coaxial cable

Single cable jack*	CA-CJH- <u>CC</u> 3
	SC-CJ- <u>CC</u> ⁴

Telephone jacks



6-conductor telephone jack, RJ11

SC-PJ-CC⁴

Single telephone jack* CA-PJH-CC3

CC²: Gloss and Stainless Steel color codes, see pg. 161

<u>CC</u>³: Gloss color codes, see pg. 161

CC⁴: Satin color codes, see pg. 161

Receptacles



Tamper resistant receptacles

15A, 125V*	CARS-15-TR- <u>CC</u> 3
	SCRS-15-TR- <u>CC</u> ⁴
20A, 125V*	SCRS-20-TR- CC ⁴

Receptacles

·	
15A, 125V*	CAR-15H- <u>CC</u> 3
	SCR-15- <u>CC</u> ⁴
20A, 125V*	SCR-20- <u>CC</u> ⁴

GFCI Receptacles



- Press test button to confirm LED indicator status
- Press reset button to reset GFCI after circuit interruption

Tamper resistant GFCI receptacles

•	•	
15A, 125V*	GFCI	CAR-15-GFTR- CC ³
		SCR-15-GFTR- CC ⁴
20A, 125V*	GFCI	SCR-20-GFTR- <u>CC</u> ⁴

Receptacles for dimming use



- Duplex for dimming both connected loads
- Projecting nubs prevent standard plugs from being used
- Requires replacement plugs for dimming use

Duplex for dimming use

15A	120/125V*	CAR-15-DFDU- <u>CC</u> ²
15A	120/125 V*	SCR-15-DFDU- <u>CC</u> 4
20 A	120/125V*	CAR-20-DFDU- <u>CC</u> ²
20A	120/125 V*	SCR-20-DFDU- <u>CC</u> 4

Receptacles for dimming use



- Top half for dimming
- Projecting nub prevents standard plug from being used
- Requires replacement plugs for dimming use
- Bottom half is a general use receptacle and will fit standard duplex plugs

Split duplex (half for dimming use)

15A	120/125V*	CAR-15-HFDU- <u>CC</u> 2
15A	120/125V*	SCR-15-HFDU- <u>CC</u> ⁴
20A	120/125V*	CAR-20-HFDU- <u>CC</u> ²
20 A	120/125V*	SCR-20-HFDU- <u>CC</u> ⁴

Receptacles for dimming use



- Duplex for dimming both connected loads
- Projecting nubs prevent standard plugs from being used
- Requires replacement plugs for dimming use
- 15A model shown
- Tamper resistant shutter mechanism

Dual dimming tamper resistant

15A	120/125V*	CAR-15-DDTR- <u>CC</u> ²
15A	120/125V*	SCR-15-DDTR- <u>CC</u> ⁴
20A	120/125V*	CAR-20-DDTR- CC ²
20 A	120/125 V*	SCR-20-DDTR-CC

Receptacles for dimming use



- Top half for dimming
- Projecting nub prevents standard plug from being used
- Requires replacement plugs for dimming use
- Bottom half is a general use receptacle and will fit standard duplex plugs
- 15A model shown
- Tamper resistant shutter mechanism

Half dimming tamper resistant

15A	120/125V*	CAR-15-HDTR- <u>CC</u> ²
15A	120/125V*	SCR-15-HDTR- <u>CC</u> ⁴
20A	120/125V*	CAR-20-HDTR- <u>CC</u> 2
20A	120/125V*	SCR-20-HDTR- <u>CC</u> ⁴

CC²: Gloss color code and Stainless Steel,

see pg. 161

CC4: Satin color codes, see pg. 161

Replacement plug for dimming (use with receptacles on left)



- This plug required for use with Lutron® receptacles for dimming use—plug will work in standard receptacle
- Easily replaces the existing plugs on lamps

120/125V	RP-FDU-10-WH
White	
120/125V	RP-FDU-10-BR
Brown	

UL/CSA/NOM regulatory approvals.

Important notes

- If the hot and dimmed hot feeds to the split duplex HFDU are supplied from different circuits or split-wired with separate switch-legs, a means to simultaneously disconnect these circuits must be provided at the panel board where they originate (NEC 210.7(C) 2002 Edition). A 2-pole circuit breaker or two single-pole circuit breakers with an approved handle tie can be used to accomplish this simultaneous disconnect. Feed-through dimming panels, which are those without breakers, are recommended when using the HFDU.
- Receptacles and plugs for dimming use are UL listed for use with all Lutron® wallbox dimmers included in this catalog.
- If there is only one electrical feed to the receptacle, then the duplex DFDU must be used.
- For detailed information, see Application Notes #91 (Guide to Dimming Table Lamps) and #109 (Guide to Dimming Portable Lamps via Receptacles) at www.lutron.com/applicationnotes.

CC²: Gloss color code and Stainless Steel, see pg. 161

CC4: Satin color codes, see pg. 161

Field customizable 6-port frame



- Shipped with six blanks in matching colors
- Connectors and wallplate sold separately
- Connectors snap in (no tools required)
- Connectors available in White (WH), unless noted

6-port frame*	CA-6PF- <u>CC</u> ³
	SC-6PF- <u>CC</u>⁴

Connectors for 6-port frame

Telephone/network jacks



8-conductor,	CON-1P-C3- EE ⁴
RJ45 category 3	
8-conductor,	CON-1P-C5E- EE⁴
RJ45 category 5e	
8-conductor,	CON-1P-C6- EE⁴
RJ45 category 6	

Fiber jacks



CON-1F-MTRJ-WH
CON-1F-SC-WH
CON-1F-LC-WH
CON-1F-ST-WH

Cable jack



F-style,	CON-1C- <u>EE⁴</u>
75-Ohm coaxial cable	

BNC jack



BNC connector, 50-Ohm	CON-1B-WH

Connectors only for use with 6-port frame.

Switches



- · Paddle turns on/off
- · Use with any 15A load
- General purpose switching of all sources and motor loads
- · No derating if ganged

General purpose switches (120/277 V)

CA-1PSH- CC ³
5
SC-1PS- <u>CC</u> ⁴
CA-3PSH- <u>CC</u> 3
SC-3PS- <u>CC</u> ⁴
CA-4PSH- CC ³
SC-4PS- <u>CC</u> ⁴

General purpose switch with locator light (120 V only)

Single-pole	15A*	CA-1PSNL- EE ²
		SC-1PSNL- <u>EE</u> 10
3-way	15A*	CA-3PSNL- EE 2
		SC-3PSNL- <u>EE</u> 10
4-way	15A*	CA-4PSNL- <u>EE</u> 2
		SC-4PSNL- <u>EE</u> 10

CC³: Gloss color codes, see pg. 161

CC⁴: Satin color codes, see pg. 161

EE²: Only available in Almond (AL), Ivory (IV), Light Almond (LA) and White (WH)

<u>EE</u>⁴: Only available in White (WH) and Black (BL)

EE¹⁰: Available in Biscuit (BI), Eggshell (ES), Goldstone (GS), Limestone (LS), Sea Glass (SG) and Snow (SW)

How to understand ganging and derating

Standard ganging

Ganging is the side-by-side mounting of two or more dimmers or accessory devices under a multi-gang wallplate.

Standard multi-gang installation:

- Uses standard multi-gang electrical backboxes
- Uses standard multi-gang wallplates
- Requires fins to be removed from dimmers for proper spacing ("Fins Broken" ganging)
- May require derating (i.e., reduction of dimmer capacity due to fin removal), see Derating Tables, pgs. 172–173

Custom ganging for Architectural style controls

For Architectural style dimmers and switches, it is possible to retain the maximum capacity of dimmers in multi-gang applications via custom architectural multi-gang:

- May require customized, wider-thanstandard wallplates
- May require wider-than-standard electrical backboxes
- · Allows full capacity ("No Fins Broken") ganging
- Required for Nova® dimmers and for larger width (high capacity) architectural controls
- Visit www.lutron.com/customganging for additional information

Standard ganging for dimmers, switches and accessories

New Architectural Architectural Designer Traditional pg. 148 pg. 160 pg. 152 pg. 166 F Vierti_® Vareo_® Maestro Abella® Nova T☆® Maestro IR® Ceana® Maestro Wireless® Ariadnia Spacer System® Glyder_® Diva_® Rotary Lyneo_® Lx Skylark_® Skylark Contour_{TM} Derating Table 1 Derating Table 2 Derating Table 1 **Derating Table 1** pg. 172 pg. 173 pg. 172 pg. 172 www.lutron.com | 1.800.523.9466 | **LUTRON**

Standard ganging and fins broken derating examples:



One Nova T☆® dimmer



No fins broken Full capacity



Standard 1-gang backbox



Standard 1-gang architectural wallplate



Two Nova T☆ dimmers "Fins Broken" ganging




One fin broken* Partial derating




Standard 2-gang backbox



Standard 2-gang architectural wallplate




Three Nova T☆ dimmers "Fins Broken" ganging




Inside: Two fins broken*
Full derating

Outside: One fin broken*



Standard 3-gang backbox



Standard 3-gang architectural wallplate

Custom Architectural ganging example:



Two Nova T☆ dimmers "No Fins Broken" ganging




Partial derating

No fins broken Full capacity



Backbox with chase nipple



Custom architectural wallplate

For further information on ganging and derating, visit www.lutron.com/multigang.

*The fins are scored and designed to be removed easily.

Appendix | Ganging and derating

Derating Table 1

New Architectural | Vierti®

Designer | Maestro®, Maestro IR®, Maestro Wireless®, Spacer System®, Diva®, Lyneo® Lx, Skylark Contour™, Skylark® **Traditional** | Abella®, Ceana®, Ariadni®, Glyder®, Rotary

	No fins broken	1 fin broken	ূ্ৰ 2 fins broken
Incandescent			
Dimmers	600W	500W	400 W
	1000W	800W	650W
Dual dimmers	300W	250W	200 W
	300W	250W	200 W
Magnetic low-voltage			
Dimmers	600 VA / 450 W	500 VA / 400 W	400 VA/300 W
	1000 VA/800 W	800 VA / 650 W	650 VA/500 W
Electronic low-voltage			
Dimmers	300W	250W	200 W
	500 W	450W	400 W
	600 W	500 W	400 W
Fluorescent			
Hi-lume _® /Hi-lume _® Compact SE/Eco-10 _® /	EcoSystem _®		
Vierti	60 ballasts/6A	50 ballasts/5A	35 ballasts/3.5A
Maestro/Spacer System	20 ballasts/6A	20 ballasts/5A	20 ballasts/3.5A
Diva, Skylark, Lyneo Lx and Ariadni	no derating	no derating	no derating
Tu-Wire®: Spacer System, Diva, Skylark	5A	4A	3.3A
Fan controls			
Quiet 7-speed	1.0A/300W	1.0A/300W	1.0A/300W
Quiet 3-speed	1.5A	1.5A	1.5A
Fully variable	5A	4A	3A
Fan/light controls			
Quiet 7-speed	1.0A/300W	1.0A/300W	1.0A/300W
Quiet 3-speed	1.5A/300W	1.5A/300W	1.5A/300W
	1.5A/360W	1.5A/360W	1.5A/360W
Fully variable	2.5A/300W	2.1A/250W	1.7A/200W
Electronic switches			
Vierti	6A/3A	5A/3A	3.5A/3A
Maestro (light/fan)	8A/3A	6.5A/3A	5A/3A
Abella (light/fan)	6A/3A	5A/3A	3.5A/3A

Appendix | Ganging and derating

Derating Table 2

Architectural | Vareo®, Nova T☆®

	শূরী No fins broken	្រី 1 fin broken	2 fins broken
Incandescent			
Dimmers	600 W	500W	300W
	1000W	900W	700W
	1500W	1250W	1000W
	1950W	_	_
Magnetic low-voltage	·	^	
Dimmers	600 VA / 450 W	500 VA /400 W	300 VA/250 W
	1000 VA/800 W	900 VA / 750 W	700 VA/500 W
	1500 VA/1200 W	1250 VA / 1000 W	1000 VA/800 W
Electronic low-voltage	·		
Dimmers	300W	300W	250W
	600 W	500W	400 W
Fluorescent		^	
Hi-lume®/Hi-lume® Compact SE/	Eco-10⊛/EcoSystem®		
Vareo	20 ballasts/8A	20 ballasts/6A	20 ballasts/4.5 A
Nova T☆	6A	no derating	no derating
	8A	no derating	no derating
	16A	no derating	no derating
0-10 VDC control ¹	30 mA ballasts	no derating	no derating
Tu-Wire®	5A	4A	3.3A
Fan controls			
Quiet 3-speed	1.5A	no derating	no derating
Fully variable	6A	4.2 A	2.5 A
Fully variable	12A	10A	8.3A
Electronic tapswitches ²			
VETS-1000-	1000W	800W	650W
VETS-1000-SL-	1000W	900 W	700 W
VETN-1000-	1000 VA	700 VA	550 VA

For further information on ganging Nova®, visit www.lutron.com/customganging.

¹PowerPack required for line voltage switching.

²VETS-R-Auxiliary electronic tapswitches do not require derating.

Dimmer capabilities and interface requirements

Multi-location—true dimming from each location

eco-model available

Compatible dimmer (no interface)

WBX TVI 3F PA Requires interface, see notes below



Dimmers	capacity [†]	0				
	600 W			W		
	1000 W			O		
	1500W		WBX			
	2000 W		WBX			
Magnetic low-voltage 120V	600 VA (450 W)					
	1000 VA (800 W)					
	1500 VA (1200 W)		WBX			
	2000 VA (1600 W)		WBX	WBX		
▼ Magnetic low-voltage 277∨	600 VA (450 W)		WBX		WBX	
	1000 VA (800 W)		WBX		WBX	
₩ Electronic low-voltage 120V	300W		WBX			
	450W		WBX	WBX		
	600W		WBX		WBX	
₩ Electronic low-voltage 277 V	16A		WBX	WBX	WBX	
Neon/cold cathode			WBX	WBX		
ঞ্®3-wire ballasts and Hi-lume⊚ LE	ED driver 120V 6A					
Hi-lume, Hi-lume Compact SE,	8A					
Eco-10 _® and EcoSystem _® ballasts	16A		3F			
☑ 3-wire ballasts and Hi-lume LED driver 277 V 6A			3F			
Hi-lume, Hi-lume Compact SE,	8A		3F			
Eco-10 and EcoSystem ballasts	16A		3F	3F	3F	
ℤ⊭ Tu-Wire ballasts 120V	5A		PA			
☞⊚0-10 VDC (ballasts or LED Drivers) 120/277V 16A	TVI	TVI			

WBX: Wallbox Phase Adaptive Power Module

(PHPM-WBX-DV-WH)

3F: Fluorescent Power Module

(PHPM-3F-DV-WH)

TVI: 0-10 V Interface

(GRX-TVI)

PA: Phase Adaptive Power Module

(PHPM-PA-DV-WH)

See pgs. 178–179 for specific compatible dimmer models and switching interface solutions.

*Consult Lutron Technical Support for information on interfaces with Vierti.

[†]UL listed for FULL wattage indicated (derate capacity only if ganged with other devices).

Dimmer capabilities and interface requirements

Multi-location—true dimming from each location

eco-model available

Compatible dimmer (no interface)

WBX TVI 3F PA Requires interface, see notes below



Dimmers capacity [†]				Ø	
600 W	(3				3
1000W					
1500W	WBX		WBX	WBX	WBX
2000W	WBX		WBX	WBX	WBX
600 VA (450 W)					
1000 VA (800 W)					
1500 VA (1200 W)	WBX		WBX	WBX	WBX
2000 VA (1600 W)	WBX		WBX	WBX	WBX
600 VA (450 W)	WBX		WBX	WBX	WBX
1000 VA (800 W)	WBX		WBX	WBX	WBX
300W			WBX		
450W			WBX		WBX
600W			WBX		WBX
16A	WBX		WBX	WBX	WBX
			WBX		WBX
D driver 120V 6A					
8A	3F		3F	3F	
16A	3F		3F	3F	3F
driver 277V 6A					
8A	3F		3F	3F	3F
16A	3F		3F	3F	3F
5A	PA		PA		
120/277V 16A	TVI		TVI	TVI	TVI
	600 W 1000 W 1500 W 2000 W 600 VA (450 W) 1000 VA (800 W) 1500 VA (1200 W) 2000 VA (1600 W) 600 VA (450 W) 1000 VA (800 W) 300 W 450 W 600 W 16 A D driver 120 V 6 A 8 A 16 A 0 driver 277 V 6 A 8 A 16 A 5 A	600W 1000W 1500W WBX 2000W WBX 600VA (450W) 1000VA (800W) 1500VA (1200W) WBX 2000VA (1600W) WBX 600VA (450W) WBX 300W 450W 600W 16A WBX D driver 120V 6A 8A 3F 16A 3F 16A 3F 16A 3F 16A 3F 16A 3F	600W 1000W 1500W WBX 2000W WBX 600VA (450W) 1000VA (800W) 1500VA (1200W) WBX 2000VA (1600W) WBX 600VA (450W) WBX 300W 450W 600W 16A WBX D driver 120V 6A 8A 3F 16A 3F 16A 3F 16A 3F 16A 3F 16A 3F 16A 3F	600 W 1000 W WBX WBX 2000 W WBX WBX 2000 W WBX WBX 600 VA (450 W) 1500 VA (1200 W) 2000 VA (1600 W) WBX WBX 600 VA (450 W) WBX WBX 600 VA (450 W) WBX WBX WBX 1000 VA (800 W) WBX WBX WBX 300 W WBX WBX 450 W WBX MBX MBX D driver 120 V 6 A 8 A 3F 3F 16 A 3F 3F	600W 1000W 1500W WBX WBX WBX WBX 2000W WBX WBX WBX WBX WBX WBX WBX WBX WBX WB

WBX: Wallbox Phase Adaptive Power Module

(PHPM-WBX-DV-WH)

3F: Fluorescent Power Module

(PHPM-3F-DV-WH)

TVI: 0-10 V Interface

(GRX-TVI)

PA: Phase Adaptive Power Module

(PHPM-PA-DV-WH)

See pgs. 178–179 for specific compatible dimmer models and switching interface solutions.

†UL listed for FULL wattage indicated (derate capacity only if ganged with other devices).

Dimmer capabilities and interface requirements

Multi-location—true dimming from each location

eco-model available

Compatible dimmer (no interface)

WBX TVI 3F PA Requires interface, see notes below



			Pg. 100		
Dimmers	capacity [†]				W
	600 W		•	•	
	1000 W				
	1500 W	WBX		WBX	
	2000 W	WBX		WBX	
▼ Magnetic low-voltage 120V	600 VA (450 W)				
	1000 VA (800 W)			WBX	
	1500 VA (1200 W)	WBX		WBX	
	2000 VA (1600 W)	WBX		WBX	
▼ Magnetic low-voltage 277 ∨	600 VA (450 W)	WBX		WBX	
	1000 VA (800 W)	WBX		WBX	
₩ Electronic low-voltage 120 V	300 W				
	450W			WBX	
	600W			WBX	
ਓ Electronic low-voltage 277 V	16A	WBX		WBX	
_ Neon/cold cathode		WBX		WBX	
್ರಾಂ 3-wire ballasts and Hi-lume ⊗ LE	D driver 120V 6A				
Hi-lume, Hi-lume Compact SE,	8A				
Eco-10 _® and EcoSystem _® ballasts	16A	3F		3F	
್ರಾ⊚3-wire ballasts and Hi-lume LEI	Odriver 277V 6A				
Hi-lume, Hi-lume Compact SE,	8A	3F		3F	
Eco-10 and EcoSystem ballasts	16A	3F		3F	
∠-Tu-Wire ballasts 120 V	5A	PA			
☞ 0-10 VDC (ballasts or LED Drivers	120/277V 16A	TVI		TVI	

WBX: Wallbox Phase Adaptive Power Module

(PHPM-WBX-DV-WH)

3F: Fluorescent Power Module

(PHPM-3F-DV-WH)

TVI: 0-10 V Interface

(GRX-TVI)

PA: Phase Adaptive Power Module

(PHPM-PA-DV-WH)

See pgs. 178–179 for specific compatible dimmer models and switching interface solutions.

†UL listed for FULL wattage indicated (derate capacity only if ganged with other devices).

Dimmer capabilities and interface requirements

Multi-location—true dimming from each location

eco-model available

Compatible dimmer (no interface)

WBX TVI 3F PA Requires interface, see notes below



Dimmers	capacity [†]		
☐ Incandescent/halogen 120V	600 W	9	a
	1000 W		
	1500W	WBX	
	2000 W	WBX	
∀ Magnetic low-voltage 120 V	600 VA (450 W)		
	1000 VA (800 W)		
	1500 VA (1200 W)	WBX	
	2000 VA (1600 W)	WBX	
▼ Magnetic low-voltage 277 V	600 VA (450 W)	WBX	
	1000 VA (800 W)	WBX	
₩ Electronic low-voltage 120V	300W	WBX	
	450W	WBX	
	600W	WBX	
₩ Electronic low-voltage 277 V	16A	WBX	
Neon/cold cathode		WBX	
ಾ್®3-wire ballasts and Hi-lume® LE	D driver 120V 6A		
Hi-lume, Hi-lume Compact SE,	8A		
Eco-10 _® and EcoSystem _® ballasts	16A	3F	
್ರಾ⊛3-wire ballasts and Hi-lume LEI	Odriver 277 V 6A		
Hi-lume, Hi-lume Compact SE,	8A	3F	
Eco-10 and EcoSystem ballasts	16A	3F	
Z: Tu-Wire	5A	PA	
☞/◎0-10VDC (ballasts or LED Drivers)	120/277V 16A	TVI	

WBX: Wallbox Phase Adaptive Power Module

(PHPM-WBX-DV-WH)

3F: Fluorescent Power Module

(PHPM-3F-DV-WH)

TVI: 0-10V Interface

(GRX-TVI)

PA: Phase Adaptive Power Module

(PHPM-PA-DV-WH)

See pgs. 178–179 for specific compatible dimmer models and switching interface solutions.

†UL listed for FULL wattage indicated (derate capacity only if ganged with other devices).

Dimmer models/load interface compatibility

	Incandescent, magnetic and electronic low-voltage (120/277 V)		and electronic ballasts or Hi-lume⊚		0-10 VDC Ballasts or LED drivers (120/277 V)	
	WBX		3F		TVI	
	Wallbox Phas Power Modul	le*	Fluorescent Power Modu		0-10 V Interface	
	PHPM-WBX-	-DV-WH	PHPM-3F-D)V-WH	GRX-TVI	
Dimmer Family	Single- pole	3-way or multi-location	Single- pole	3-way or multi-location	Single- pole	3-way or multi-location
Abella®	_	_	_	_	_	_
Ariadni®	_	AYF-103P-	_	AYF-103P-	_	AYF-103P-
Ceana®	_	_	_	_	_	_
Diva _® Gloss	_	DVF-103P-	_	DVF-103P-	-	DVF-103P-
Diva Satin Colors®	_	DVSCF- 103P-	_	DVSCF- 103P-	_	DVSCF- 103P-
Glyder _®	_	_	_	_	_	_
Lyneo _® Lx	_	LXF-103PL-	_	LXF-103PL-	_	LXF-103PL-
Maestro® Gloss	_	MAF-6AM-	_	MAF-6AM-	_	MAF-6AM-
Maestro® Satin Colors®	_	MSCF-6AM-	_	MSCF-6AM-	_	MSCF-6AM-
Maestro Wireless®	_	MRF2- F6AN-DV-	_	MRF2- F6AN-DV-	_	MRF2- F6AN-DV-
Nova®	NF-10-	NF-103P-	NF-10-	NF-103P-	NF-10-	NF-103P-
Nova T☆®	NTF-10-	NTF-103P-	NTF-10-	NTF-103P-	NTF-10-	NTF-103P-
Skylark _®	SF-10P-	SF-103P-	SF-10P-	SF-103P-	SF-10P-	SF-103P-
Spacer System®	_	SPSF-6AM-	_	SPSF-6AM-	SPSF-S6A-	SPSF-6AM-
Vareo®	_	VF-10-	_	VF-10-	_	VF-10-
Vierti®	conta	ct Lutron	conta	contact Lutron		VTF-6AM-

Use only dimmer model numbers listed.

^{*}Dual 120/277 V model given,120 V only versions are also available. Please see Technical notes, pg. 179.

Dimmer models/load interface compatibility

	Tu-Wire⊚ Fluorescent Ballasts (120 V)		Switched Lighting (120/277 V)	
	PA		sw	
	Phase Adaptive Power Module* PHPM-PA-DV-WH		Switching Power Module* PHPM-SW-DV-WH	
Dimmer Family	Single- pole	3-way or multi-location	Single- pole	3-way or multi-location
Abella®	_	_	_	AB-S6AM-
Ariadni®	_	AYF-103P-	_	_
Ceana®	_	_	_	_
Diva _® Gloss	_	DVF-103P-	_	_
Diva Satin Colors®	_	DVSCF-103P-	_	_
Glyder®	_	_	_	_
Lyneo _® Lx	_	LXF-103PL-	LX-1PSL-	LX-3PSL-
Maestro _® Gloss	_	MAF-6AM-	_	MA-S8AM-
Maestro® Satin Colors®	_	MSCF-6AM-	_	MSC-S8AM-
Maestro Wireless®	_	MRF2- F6AN-DV-	_	MRF2-6ANS-
Nova _®	NF-10-	NF-103P-	_	_
Nova T☆®	NTF-10-	NTF-103P-	_	_
Skylark _®	SF-10P-	SF-103P-	_	_
Spacer System _®	SPSF- S6A-	SPSF-6AM-	SPSF- S6A-	SPSF-S6AM-
Vareo _®	_	VF-10-	_	VETN-1000-
Vierti®	contact Lutron		contact Lutron	

Technical notes

- Lighting load interfaces must be matched to load type and voltage
- All load interfaces for dimmed load are controlled by a 120 V 3-wire fluorescent dimmer
- Power feed to dimmer may differ from lighting load/interface voltage
- Interfaces typically require additional power feeds
- For wiring information, consult wiring diagrams, see pgs. 193-195
- For assistance and additional solutions, consult Lutron Technical Support at 1.800.523.9466 (24 hours/7 days)


Interface mounting

- PHPM interfaces mount to 2-gang electrical backbox (W: 6.30 in x H: 5.10 in)
- GRX-TVI enclosure is surface mount only (W: 6.10 in x H: 12.50 in x D: 3.30 in)

Use only dimmer model numbers listed.

*Dual 120/277 V model given, 120 V only versions are also available. Please see Technical notes, pg. 179.

Skylark Contour™



For illustration purposes only. Consult model number pages for specific voltage and capacity information.

www.lutron.com | 1.800.523.9466 | **LUTRON**.